



Tygon® E-1000

Pumpable Tubing for Food & Beverage Dispensing

Soft and flexible, Tygon® E-1000 tubing delivers superior performance in a formulation that contains non-DEHP [Bis (2-ethylhexyl) phthalate] plasticizers. Tygon® E-1000 non-DEHP tubing has been tested rigorously to meet stringent standards for low temperature and corrosive chemical resistance.

Ideal Selection for Complex Set-Ups

Tygon® E-1000 tubing is an excellent solution to applications requiring complicated set-ups with sharp radius curves and multiple directional changes. Tygon® E-1000 tubing resists twisting and collapse, which are common problems when using other tubing products. Tygon® E-1000 tubing stays flexible at temperatures as low as -67°F (-55°C).

The Preferred Tubing in Low-Torque Peristaltic Pumps

The extremely low durometer (40) of Tygon® E-1000 tubing provides minimal resistance to compression. This feature is ideal when using low-torque or battery-driven peristaltic pumps. Tygon® E-1000 tubing provides an excellent alternative to silicone tubing where corrosive chemicals are used.

Tygon® E-1000 tubing will typically outlast silicone tubing in peristaltic pump applications by a margin of 2 to 1.

FAVS
Scientific Equipment
di Gnudi Andrea e Antonella S.r.l.
Tel. 051501153
www.favs.it • info@favs.it



Features and Benefits

- Soft and flexible
- Low-temperature resistant
-67°F (-55°C)
- Resistant to corrosive chemicals
- Low durometer for use in low-torque pump applications
- Meets the requirements of applicable FDA Food Additive Regulations*

Typical Applications

- Peristaltic pumps
- Vent and drain lines

* Use restrictions and limitations may apply.


SAINT-GOBAIN

Tygon E-1000

Part Number	ID		OD		Wall Thickness		Min. Bend Radius		Max. Working Pressure		Vacuum Rating	
	(in)	(mm)	(in)	(mm)	(in)	(mm)	(in)	(mm)	73°F (psi)*	23°C (bar)*	73°F (inHg)	23°C (mmHg)
ADK00003	1/16	1.59	3/16	4.76	1/16	1.59	1/8	3.18	26	1.8	29.9	760
ADK00007	1/8	3.18	1/4	6.35	1/16	1.59	3/8	9.53	16	1.1	29.9	760
ADK00012	3/16	4.76	5/16	7.94	1/16	1.59	5/8	15.88	10	0.7	15.0	381
ADK00017	1/4	6.35	3/8	9.53	1/16	1.59	1	25.40	8	0.6	7.0	178
ADK00019	1/4	6.35	1/2	12.70	1/8	3.18	5/8	15.88	14	0.9	29.9	760
ADK00022	5/16	7.94	7/16	11.11	1/16	1.59	1-3/8	34.93	7	0.5	5.0	127
ADK00027	3/8	9.53	1/2	12.70	1/16	1.59	1-3/4	44.45	7	0.5	3.0	76
ADK00029	3/8	9.53	5/8	15.88	1/8	3.18	1-1/8	28.58	11	0.8	15.0	381
ADK00036	1/2	12.70	5/8	15.88	1/16	1.59	2-7/8	73.03	6	0.4	2.0	51
ADK00038	1/2	12.70	3/4	19.05	1/8	3.18	1-3/4	44.45	8	0.6	7.0	178

* Working pressures are calculated at a 1:5 ratio relative to burst pressure using ASTM D1599. Additional sizes available upon request.

Relative Chemical Resistance Properties*

Acids			Bases			Salts	Alcohols	Ketones
Conc.	Med.	Weak	Conc.	Med.	Weak			
F	E	E	E	E	E	E	F	U

E = Excellent F = Fair U = Unsatisfactory

* All tests conducted at room temperature.

Typical Physical Properties

Property	ASTM Method	Value or Rating
Durometer Hardness (Shore A), 15 sec	D2240	40
Color	—	Clear
Opacity	—	Translucent
Tensile Strength, psi (MPa)	D412	1100 (7.6)
Ultimate Elongation, %	D412	435
Tear Resistance, lb-f/in (kN/m)	D1004	104 (18.2)
Specific Gravity	D792	1.10
Water Absorption, % at 73°F (23°C) for 24 hrs	D570	0.29
Compression Set Constant Deflection, % at 158°F (70°C) for 22 hrs	D395	55
Maximum Recommended Operating Temp., °F (°C)	—	125 (52)
Brittleness by Impact Temp., °F (°C)	D746	-67 (-55)
Tensile Stress, psi (MPa) @ 100% Elongation	D412	286 (2.0)

Unless otherwise noted, all tests were conducted at room temperature (73°F). Values shown were determined on 0.075" thick extruded strip or 0.075" thick molded ASTM plaques or molded ASTM durometer buttons.

Regulatory Compliance

FDA Approved for Food Contact	Yes
Contains REACH SVHC	No
NSF-51 Standard	Yes
Sterilization Methods	Gas
USP Class VI	No

The values listed for working and burst pressures are derived from tests conducted under controlled laboratory conditions. Many factors will reduce the tubing's ability to withstand pressures, including temperature, chemical attack, stress, pulsation and the attachment to fittings. It is imperative that the user conduct tests simulating the conditions of the application prior to specifying the tubing for use.

www.ics.saint-gobain.com



Saint-Gobain Performance Plastics
 2664 Gilchrist Road
 Akron, OH 44305
 1-800-798-1554
 Tel: (330) 798-9240
 Fax: (330) 798-6968

Saint-Gobain Performance Plastics
 5 rue du Dauphiné
 Zone Industrielle de Chesnes
 BP712 Saint-Quentin-Fallavier
 Cedex, France 38297
 Tel: (33) 0-4-74-94-82-34

Saint-Gobain Performance Plastics
 1476 Kun Yang Road
 Minghang Economic & Technological
 Development Zone
 Shanghai, China 200245
 Tel: (86) 21-5472-1568
 Fax: (86) 21-5472-2378/5472-2379

NOTE: The data and details given in this document are correct and up to date. This document is intended to provide information about the product and possible applications. This document is not the product specification and does not provide specific features, nor does it guarantee product performance in specific applications. Saint-Gobain cannot anticipate or control the conditions of the field and for this reason strongly recommends that practical tests are conducted to ensure that the product meets the requirements of a specific application.

Tygon[®] is a registered trademark.