



*Inverted trinocular brightfield/phase contrast microscope, IOS*

<b>Observation Method - Transmitted Light</b>	Brightfield	Yes
	Phase contrast (Positive type)	Yes
<b>Main Body</b>	Type	Inverted
	Construction material	Aluminum die-cast
<b>Head</b>	Type	Trinocular (Siedentopf)
	Split ratio	100/0 - 50/50
	Inclination	45°
	Interpupillary distance (mm)	50-75
	Diopter adjustment	On left tube
	Tube inner diameter (mm)	30
<b>Eyepieces</b>	Field number (mm)	22
	Magnification	10x
	Planar type	Yes
	Micrometric scale	As optional
	Diameter of micrometer glass (mm)	26
	High eyepoint (for glass wearers)	Yes
	Rubber cup	Yes
	Retractable protections	Yes
<b>Nosepiece</b>	Positions	Quintuple
	Reversed	Yes
	Bi-directional	Yes
	Rotation on ball bearings	Yes
	Objective thread	RMS
<b>Objectives</b>	Optical system	$\infty$
	Anti-fungus treatment	Yes
	Parfocal distance (mm)	45
	Standard magnifications	100x-400x
	Type	IOS LWD W-PLAN PH
		IOS LWD W-PLAN PH 10x/0.25, W.D. 7.3 mm
		IOS LWD W-PLAN PH 20x/0.40, W.D. 6.8 mm
		IOS LWD W-PLAN PH 40x/0.65, W.D. 3.0 mm

<b>Stage</b>	Type	Fixed
	Dimensions (mm)	250x160
	Material	Anti-scratch painting
	Glass round insert	Yes
	Metal round insert	Yes
	Holder for Petri dish (mm)	54 (Included), 38, 65 (As optional)
	Holder for Terasaki plate	96 well
	Holder for 1 slide	Yes
	Holder for 2 slides	As optional
	Holder for Utermöhl chamber	As optional

<b>Condenser - Single Position</b>	Type	Abbe
	Removable	Yes
	Numerical aperture (N.A.)	0.30
	Diaphragm	Iris
	Slider for phase contrast	BF, 4x/10x, 20x/40x positions
	Slider for color filters	Yes
	Long working distance	Yes
	Working distance (for LWD) (mm)	72
	Extendable working distance (for LWD) (mm)	up to 150

<b>Focusing System</b>	Type	Coaxial coarse & fine
	Focus modes	Coarse & fine
	Fine graduations	100
	Fine total travel (per single rotation) (mm)	0.2
	Fine resolution (µm)	2
	Adjustable tension	Yes

<b>Transmitted Illumination</b>	Type	X-LED
	X-LED type	X-LED8
	Light source power (W)	8
	Brightness control	Manual
	Lifetime (hours)	> 65,000
	Temperature (K)	6,300
Max. required power (W)	13	

<b>Power Supply for Transmitted Illumination</b>	Type	External
	Microscope connector	Jack, 2.1 mm
	Power plug type	Multi-plug (EU, UK, US)
	Input voltage	100/240 Vac, 50/60 Hz
Output voltage	6 Vdc 2.5 A	

<b>Accessories Included</b>	Dust cover	Yes
	Allen wrench	Yes
	Centering telescope	Yes
	Green filter	Yes
	LBD filter	Yes
	User Manual	Digital version (downloadable)

<b>Additional Information</b>		Mechanical stage dimension 250x230 mm, X-Y translation range 120x80 mm (as optional). Metallic interchangeable inserts for slides, Petri dishes, Terasaki, multi-Well plates (as optional).
-------------------------------	--	--

<b>Product Dimensions</b>	Height (mm)	495
	Width (mm)	230

Depth (mm)	540
------------	-----

<b>Product Weight</b> (kg)	9
----------------------------	---